

More power for your money:

SIMATIC IPC427C starter packages



Special package savings!
approx. 25%

Start saving right now: Our low-priced starter packages with embedded SIMATIC IPC427C industrial PC make it possible.

Starter package A – SIMATIC IPC427C

Together with the preinstalled Windows Embedded Standard 2009 operating system, a 24 V power supply, and a USB flash drive, it includes everything you need to get started right away in the Siemens embedded PC world.

For high system availability, the package also includes additional components, e.g. for efficient diagnostics.

It's a powerful package that offers powerful savings.

SIMATIC IPC427C highlights

High performance, compact dimensions:

- 1.2 GHz Intel Core2 Duo processor
- DDR3 memory technology with up to 4 GB

Rugged with high system availability:

- Fanless, battery-free design with rugged mass storage (SSD, CF)
- Reliable 24-hour continuous operation at ambient temperature up to 55 °C

Reliable with high flexibility:

- 2 MB retentive memory, of which 256 KB can be written within the buffer time
- Flexible mass storage concept with 32 GB SSD and 2x CompactFlash Cards (CFC) up to 8 GB
- Various options for DIN rail, wall, and upright mounting

Starter package B – PC I/O expansion



In addition to starter package A, you receive the central I/O expansion for your real-time capable, fast measuring and open-loop/closed-loop control tasks.

With the PCI-104 slots of the IPC427C and the expansion frame, you can integrate 12 encoder and counter interfaces and 320 digital and 120 analog I/O interfaces in an extremely compact design.

Starter package C – DC-UPS SITOP UPS500S



In addition to starter package A, you receive the SITOP UPS500S 24 V uninterruptible power supply. It is just as rugged and maintenance-free as the IPC427C and offers:

- Safe shutdown and correct restart of the IPC
- Reliable operation at temperatures up to 60 °C
- Battery-free, no cabinet ventilation necessary

SIMATIC IPC427C

Answers for industry.

SIEMENS

Order now and save approx. 25 % compared to the price of individual components!

<p>Starter package A</p> <p>SIMATIC IPC427C high-performance embedded industrial PC with additional components to increase system availability</p> <p>Further information is available at: www.siemens.com/microbox</p>	<p>SIMATIC IPC427C</p> <ul style="list-style-type: none"> • SIMATIC IPC427C: 1.2 GHz Intel® Core2 Solo processor, 1 GB RAM, hard disk, PROFIBUS interface • Windows XP Embedded operating system preinstalled • Operating system restore CD • SIMATIC PC USB FlashDrive, 2 GB • Adapter to implement DVI-I on VGA • SIMATIC PC DiagMonitor (diagnostic and alarm software) • One expansion frame for integration of a PCI-104 component • SITOP 120/230 V AC on 24 V DC power supply
<p>Starter package B</p> <p>SIMATIC IPC427C with PC IO central I/O expansion</p> <p>Further information is available at: www.siemens.com/pc-io</p>	<p>PC IO central I/O expansion</p> <ul style="list-style-type: none"> • Starter package A • PC IO central I/O expansion <ul style="list-style-type: none"> - Basic module with encoder/counter interfaces - Digital I/O module - Analog I/O module - Expansion frame for I/O module installation - Expansion frame for adaptation of encoder/counter interfaces
<p>Starter package C</p> <p>SIMATIC IPC427C with SITOP UPS500S 24 V uninterruptible power supply.</p> <p>Further information is available at: www.siemens.com/sitop-ups500</p>	<p>Maintenance-free DC-UPS SITOP UPS500S</p> <ul style="list-style-type: none"> • Starter package A • Maintenance-free SITOP UPS500S, 2.5 kW (Order No.: 6EP1933-2EC41) <ul style="list-style-type: none"> - Compact DIN rail device with long-life double-layer capacitors for energy storage at ambient temperatures up to 60 °C - Software tool supports further processing and response of the SIMATIC IPC427C (available as free download)

Order directly by fax at
+49 (0)911/9 78-33 21
Siemens AG, Infoservice AD/Z 1415-E
P.O. Box 23 48, 90713 Fürth, Germany

Or order online at the Siemens Mall:
www.siemens.com/automation/mall

You can find a contact partner in your area under:
www.siemens.com/automation/partner

<p>Yes, I would like to order</p> <p><input type="checkbox"/> Starter package A for € 1.690,-* Order No.: 6ES7647-7BF25-0AA0</p> <p><input type="checkbox"/> Starter package B for € 2.290,-* Order No.: 6ES7647-7BF26-0AA0</p> <p><input type="checkbox"/> Starter package C for € 1.890,-* Order No.: 6ES7647-7BF27-0AA0</p> <p><small>* Only one package per customer. The Standard Terms and Conditions for Products and Services of the Electrical Industry shall apply. All prices (excluding VAT) are quoted in euro ex works, excluding packaging.</small></p>	<p>Billing/delivery address:</p> <p>_____</p> <p>Company/department</p> <p>_____</p> <p>Name</p> <p>_____</p> <p>Street address</p> <p>_____</p> <p>Locality and postal code</p> <p>_____</p> <p>Telephone/fax</p> <p>_____</p> <p>Date, signature</p>
--	---

Siemens AG
Industry Sector
Industry Automation
P.O. Box 23 55
90713 FÜRTH
GERMANY

Subject to change without prior notice
Order No.: 6ZB5131-0AR02-0AA0
Dispo 06317
BR 0709 2.0 VOG 2 EN
Printed in Germany
© Siemens AG 2009

The information provided in this brochure contains descriptions or characteristics of performance, which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall exist only if expressly agreed in the terms of contract. Availability and technical specifications are subject to change without prior notice. All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.

www.siemens.com/simatic-ipc