

Zündschutzart	Ex e II Erhöhte Sicherheit		Ex de IIC Druckfeste Kapselung	
Material	Aluminium	Grauguß		
Anschlussspannung	3AC 230/400/500/690V			
Schutzart	Standard IP55, optional IP56, IP65			
Kühlart	Eigengekühlt			
	1MA7	1MA6	1MJ6	1MJ7
3000 min-1	0,18 ... 16 kW	2,5 ... 165 kW	0,37 ... 37 kW	45 ... 132 kW
1500 min-1	0,12 ... 13,5 kW	2 ... 165 kW	0,25 ... 30 kW	37 ... 132 kW
1000 min-1	0,25 ... 9,7 kW	1,3 ... 135 kW	0,25 ... 22 kW	30 ... 90 kW
750 min-1			0,37 ... 15 kW	18,5 ... 75 kW
Katalog	DA 81.1			