

Gearbox type	Helical gearbox	Parallel shaft gearbox	Bevel helical gearbox	Helical worm gearbox	Worm gearbox
Material	Aluminum \leq 15kW Cast-iron > 15kW				
Connection voltage	3AC 230/400/500/690V				
Degree of protection	IP55				
Cooling	Self-ventilated				
Efficiency	1 - 3 stage $\eta = 0,98 \dots 0,94$	2 - 3 stage $\eta = 0,96 \dots 0,94$		2-stage $\eta = 0,60 \dots 0,90$ depending on the transmission ratio	1-stage $\eta = 0,50 \dots 0,90$ depending on the transmission ratio
	2KJ10/11/12	2KJ13/14	2KJ15	2KJ16	2KJ17
Torque	20.000 Nm	20.000 Nm	20.000 Nm	1.590 Nm	224 Nm
Output speed	0,05 ... 1088 Urpm	0,05 ... 365 Urpm	0,05 ... 365 Urpm	0,05 ... 148 Urpm	14 ... 201 Urpm
Catalog	DA 87.1				