

SITEMP – Technical Data



SITEMP® PC		Zone 1/SDIP 27 Class B	SDIP 27 Class A
Chip set		iQ33	i965G
Processor	Optional	Intel® Celeron® D440 Intel® Core™ 2 Duo E6850	Intel® Prescott® 3 GHz
RAM		2/4 GB DDR2-800	512/1024/2048 MB
Drives	Standard	DVD-ROM 80 GB hard disk (optionally extendable to 320 GB)	DVD-ROM 80 GB hard disk in removable rack Floppy disk drive
	Optional	1. DVD burner 2. Hard disk in removable rack: 250 GB 3. PCMCIA rack unit with 2 slots 4. Chip card reader 5. 3.5" floppy disk	1. DVD burner 2. Hard disk in removable rack: 80 GB 3. PCMCIA rack with 2 slots 4. Chip card reader
	Empty slots	Instead of DVD-ROM DVD burner; 1x for 2nd; 2x for 3rd, 4th or 5th	Instead of DVD-ROM DVD burner 1x for 2nd or 3rd; 1x for 4th
Network card	Optional	10/100/1000 Mbit/s RJ45 and FOC 100 Mbit/s SC	FOC 100 Mbit/s ST or FOC 1000 Mbit/s ST
Interfaces	On board	Mouse/keyboard PS/2 Network 10/100/1000 Mbit/s RJ45 Audio	Mouse/keyboard (9-pin) Monitor (15-pin) Printer (25-pin)
	Optional	–	Up to: 2x USB 1.1 1x COM 1 1x COM 2 (9-pin each) SCSI (25-pin)
Graphics card	On board	Up to 256 MB RAM dynamically	Up to 256 MB RAM dynamically
	Optional	–	Radeon x300, PCIe
Operating system		Windows XP 32 bit OEM	Windows XP 32 bit OEM
Noise level without load		21 dBA	38 dBA
Ambient temperature		15 °C – 35 °C	15 °C – 35 °C
Dimensions (W x H x D)		203 x 390 x 392 mm	500 x 160 x 460 mm
Standards	Tempestrating	Zone 1/SDIP 27B	SDIP 27A
	CE certification	+	+
	Product safety	EN60950	EN60950
Accessories of overall SITEMP system			
Monitor	TFT 17" TFT 19"	+ +	– +
Keyboard		Keyboard Z1 D Keyboard Z1 UK Keyboard Z1 US	Keyboard SDIP 27A D Keyboard SDIP 27A US/Eng/Int
Mouse		Mouse Z1	Mouse SDIP 27A
Optional accessories			
Printer		On request	DIN A4
Scanner		On request	On request
Media converter		On request	