

Date: 2009-09-01	Radio Country Approval							
Country	SCALANCE W784-1 / -1RR / W744-1 / W746-1 / W747-1	SCALANCE W786-x PRO: - RJ45 HW rev. 3 (Note A) - FO HW rev. 4 (Note B) SCALANCE W786-2 HPW: - RJ45 HW rev. 4 - FO HW rev. 6	SCALANCE W788-1PRO/ -2PRO/-1RR/-2RR/W744-1PRO /W746-1PRO/W747-1RR (hardware-redesign, Note C)	SCALANCE W788-1PRO/ -2PRO/-1RR/-2RR/W744-1PRO/ W746-1PRO/W747-1RR (Note D)	IWLAN/PB Link PN IO HW rev. 3	IWLAN/PB Link PN IO HW rev. 1,2	ET200PRO, IM 154-6 PN HF IWLAN (HW rev. 01, Note E)	Mobile Panel 277(F) IWLAN V1 (Note F)
Antenna	(1)	(2)	(3)	(4)	(1)	(5)	(8)	(9)
Argentina	✓	✓	✓	✓		✓		
Australia	✓	✓	✓	✓	✓	✓		✓
Austria	✓	✓	✓	✓	✓	✓	✓	✓
Bahrain	✓	✓	✓					
Belgium	✓	✓	✓	✓	✓	✓	✓	✓
Brazil	✓	✓		✓		✓		
Bulgaria	✓	✓		✓	✓		✓	✓
Canada	✓	✓	✓	✓	✓	✓		✓
Chile	✓	✓	✓	✓	✓	✓		
China	✓	✓	✓	✓	✓	✓		
Colombia	✓	✓	✓		✓			
Cyprus	✓	✓					✓	✓
Czech Republic	✓	✓	✓	✓	✓	✓	✓	✓
Denmark	✓	✓	✓	✓	✓	✓	✓	✓
Estonia	✓	✓	✓				✓	✓
Finland	✓	✓	✓	✓	✓	✓	✓	✓
France	✓	✓	✓	✓	✓	✓	✓	✓
Germany	✓	✓	✓	✓	✓	✓	✓	✓
Great Britain = UK	✓	✓	✓	✓	✓	✓	✓	✓
Greece	✓	✓	✓	✓	✓	✓	✓	✓
Hong Kong	✓	✓	✓	✓	✓	✓		
Hungary	✓	✓	✓	✓	✓	✓	✓	✓
Iceland	✓	✓	✓	✓	✓	✓	✓	✓
India	✓	✓	✓	✓(6)	✓	✓(6)		
Ireland	✓	✓	✓	✓	✓	✓	✓	✓
Italy	✓	✓	✓	✓	✓	✓	✓	✓
Japan	✓	✓	✓	●	✓	✓		✓
Kuwait	✓(6)	✓(6)	✓(6)	●	✓(6)			
Latvia	✓	✓	✓				✓	✓
Liechtenstein	✓	✓	✓	✓	✓	✓	✓	✓
Lithuania	✓	✓	✓				✓	✓
Luxembourg	✓	✓	✓	✓	✓	✓	✓	✓
Malaysia	✓	✓	✓	✓	✓			
Malta	✓	✓	✓				✓	✓
Mexico	✓	✓	✓	✓	✓	✓		
Netherlands	✓	✓	✓	✓	✓	✓	✓	✓
Norway	✓	✓	✓	✓	✓	✓	✓	✓
Poland	✓	✓	✓	✓	✓	✓	✓	✓
Portugal	✓	✓	✓	✓	✓	✓	✓	✓
Romania	✓	✓	✓				✓	✓
Russia	✓	✓	✓	✓	✓			
Saudi Arabia	✓(6)	✓(6)	✓(6)		✓(6)			

Date: 2009-09-01	Radio Country Approval							
Country	SCALANCE W784-1 / -1RR / W744-1 / W746-1 / W747-1	SCALANCE W786-x PRO: - RJ45 HW rev. 3 (Note A) - FO HW rev. 4 (Note B) SCALANCE W786-2 HPW: - RJ45 HW rev. 4 - FO HW rev. 6	SCALANCE W788-1PRO/ -2PRO/-1RR/-2RR/W744-1PRO /W746-1PRO/W747-1RR (hardware-redesign, Note C)	SCALANCE W788-1PRO/ -2PRO/-1RR/-2RR/W744-1PRO/ W746-1PRO/W747-1RR (Note D)	IWLAN/PB Link PN IO HW rev. 3	IWLAN/PB Link PN IO HW rev. 1,2	ET200PRO, IM 154-6 PN HF IWLAN (HW rev. 01, Note E)	Mobile Panel 277(F) IWLAN V1 (Note F)
Antenna	(1)	(2)	(3)	(4)	(1)	(5)	(8)	(9)
Singapore	✓	✓	✓	●	✓			
Slovakia	✓	✓	✓	✓	✓	✓	✓	✓
Slovenia	✓	✓	✓	✓	✓	✓	✓	✓
South Africa	✓	✓	✓	✓	✓	✓		✓
South Korea	✓	✓	✓	●	✓	✓		
Spain	✓	✓	✓	✓	✓	✓	✓	✓
Sweden	✓	✓	✓	✓	✓	✓	✓	✓
Switzerland	✓	✓	✓	✓	✓	✓	✓	✓
Taiwan	✓(7)	✓(7)	✓(7)					
Turkey	✓	✓	✓	●	✓	✓	✓	
Ukraine	✓	✓	✓					
United Arab Emirates	✓(6)	✓(6)	✓(6)		✓(6)			
USA	✓(7)	✓(7)	✓(7)	✓	✓(7)	✓	✓	✓

The following antennas are approved in combination with the APs and recommended:

- (1): ANT795-4MR, ANT795-4MS, ANT795-6MN, ANT792-6MN, ANT793-6MN, ANT795-6DN, ANT792-8DN, ANT793-8DN, ANT792-4DN, ANT793-4MN, RCoax 2.4 and 5 GHz
- (2): ANT795-6MN, ANT792-6MN, ANT793-6MN, ANT795-6DN, ANT792-8DN, ANT793-8DN, ANT792-4DN, ANT793-4MN, RCoax 2.4 and 5 GHz
- (3): ANT795-4MR, ANT795-6MN, ANT792-6MN, ANT793-6MN, ANT795-6DN, ANT792-8DN, ANT793-8DN, ANT792-4DN, ANT793-4MN, RCoax 2.4 and 5 GHz
- (4): ANT795-4MR, ANT795-6MR, ANT792-8DR, ANT793-8DR, ANT792-4DN, ANT793-4MN, RCoax 2.4 and 5 GHz
- (5): ANT795-4MR, ANT795-4MS, ANT795-6MR, ANT792-8DR, ANT793-8DR, ANT792-4DN, ANT793-4MN RCoax 2.4 and 5 GHz
- (6) for these components only the 2,4 GHz band is approved
- (7) the antenna ANT793-8DN is not approved for this country
- (8): ANT IM 154-6 IWLAN, ANT792-6MN, ANT792-4DN, ANT793-4MN, ANT793-6MN
- (9): internal antenna of Mobile Panel 277(F) IWLAN
- : Only W788-1PRO/-2PRO and W744-1PRO are approved

**Note A)** Summary of the following products (MLFB)

W786-1PRO 6GK5786-1AA60-xxxx

6GK5786-1BA60-xxxx

W786-2 PRO 6GK5786-2AA60-xxxx

6GK5786-2BA60-xxxx

W786-3 PRO 6GK5786-3AA60-xxxx

**Note B)** Summary of the following products (MLFB)

W786-1PRO 6GK5786-1AB60-xxxx

6GK5786-1BB60-xxxx

W786-2 PRO 6GK5786-2AB60-xxxx

6GK5786-2BB60-xxxx

W786-3 PRO 6GK5786-3AB60-xxxx

Date: 2009-09-01	Radio Country Approval							
Country	SCALANCE W784-1 / -1RR / W744-1 / W746-1 / W747-1	SCALANCE W786-x PRO: - RJ45 HW rev. 3 (Note A) - FO HW rev. 4 (Note B) SCALANCE W786-2 HPW: - RJ45 HW rev. 4 - FO HW rev. 6	SCALANCE W788-1PRO/ -2PRO/-1RR/-2RR/W744-1PRO /W746-1PRO/W747-1RR (hardware-redesign, Note C)	SCALANCE W788-1PRO/ -2PRO/-1RR/-2RR/W744-1PRO/ W746-1PRO/W747-1RR (Note D)	IWLAN/PB Link PN IO HW rev. 3	IWLAN/PB Link PN IO HW rev. 1,2	ET200PRO, IM 154-6 PN HF IWLAN (HW rev. 01, Note E)	Mobile Panel 277(F) IWLAN V1 (Note F)
Antenna	(1)	(2)	(3)	(4)	(1)	(5)	(8)	(9)

**Note C)** Summary of the following products (MLFB)

W788-1PRO 6GK5788-1AA60-xxxx  
W788-2PRO 6GK5788-2AA60-xxxx  
W788-1RR 6GK5788-1AA60-xxxx  
W788-2RR 6GK5788-2AA60-xxxx  
W744-1PRO 6GK5744-1AA60-xxxx  
W746-1PRO 6GK5746-1AA60-xxxx  
W747-1RR 6GK5747-1AA60-xxxx

**Note D)** Summary of the following products (MLFB)

W788-1PRO 6GK5788-1ST00-xxxx  
W788-2PRO 6GK5788-2ST00-xxxx  
W788-1RR 6GK5788-1SR00-xxxx  
W788-2RR 6GK5788-2SR00-xxxx  
W744-1PRO 6GK5744-1ST00-xxxx  
W746-1PRO 6GK5746-1ST00-xxxx  
W747-1RR 6GK5747-1SR00-xxxx

**Note E)** Summary of the following products (MLFB)

IM 154-6 PN HF IWLAN 6ES7154-6ABxx-xxxx

**Note F)** Summary of the following products (MLFB)

Mobile Panel 277(F) IWLAN 6AV6645-0Dxxx-xxxx  
Mobile Panel 277F IWLAN **USA** 6AV6645-0Gxxx-xxxx  
Mobile Panel 277 IWLAN **USA** 6AV6645-0Fxxx-xxxx

For further details please contact our customer support, I IA AS CS1, Tel.: +49 180/5050-222  
contact form: <http://www.siemens.de/automation/support-request>