

Temperature/time classes	F200/F300				F400	
Material	Aluminum	Cast-iron	Aluminum	Cast-iron		
Connection voltage	3AC 230/400/500/690V					
Degree of protection	Standard IP55, optional IP65					
Cooling	self-ventilated		Forced-air cooled		self-ventilated	Forced-air cooled
	1LA7/1LA5	1LG6	1PP7/1PP5	1PP6	1LA6/1LG6	1PP6
3000 rpm	0,75 ... 45 kW	55 ... 200 kW	0,75 ... 45 kW	55 ... 200 kW	3 ... 190 kW	3 ... 190 kW
1500 rpm	0,55 ... 45 kW	55 ... 200 kW	0,55 ... 45 kW	55 ... 200 kW	2,2 ... 200 kW	2,2 ... 200 kW
1000 rpm	0,37 ... 30 kW	37 ... 160 kW	0,37 ... 30 kW	37 ... 160 kW	1,5 ... 160 kW	1,5 ... 160 kW
1500/3000 rpm	0,14 ... 15,3 kW		0,14 ... 15,3 kW		0,52 ... 13,6 kW	0,52 ... 13,6 kW
1000/1500 rpm	0,11 ... 8,6 kW		0,11 ... 8,6 kW		0,48 ... 9,6 kW	0,48 ... 9,6 kW
750/1500 rpm	0,09 ... 6,8 kW		0,09 ... 6,8 kW		0,3 ... 11,2 kW	0,3 ... 11,2 kW
Catalog	DA 81.1					