


I A I B I C I D I E I F I G I H I I I J I



CABLE LENGTH
5 m (16.5 FT.)
10 m (33 FT.)
30 m (98 FT.)

THREAD TYPE
1" NPT
1" BSP

- NOTES:**
- 1) THIS TRANSDUCER IS:
FM APPROVED FOR CLASS 1, ZONE 1, AEx m II T6
CENELEC APPROVED FOR EEx m II T6, ATEX CE II 2G
CSA APPROVED FOR CLASS 1 DIV.2, GROUP A,B,C & D
AND CLASS II, DIV.1, GROUP E,F, & G
 - 2) THE OPERATING TEMPERATURE RANGE IS -20° C TO 65° C.
 - 3) FOR COMPLETE MOUNTING, INSTALLATION AND
WIRING INFORMATION, REFER TO THE CUSTOMER
WIRING DIAGRAM, INSTRUCTION MANUAL OR
CONTACT THE NEAREST MILLTRONICS REPRESENTATIVE.
 - 4) ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
PRIOR NOTICE.
 - 5) EXPOSED MATERIALS: A) KYNAR FLEX AND
B) CHLOROSULPHONATED POLYETHYLENE (HYPALON).

3	ADDED THREAD TYPE BOX & CHANGED N/P INDICATOR PER ECN # 00-XR5-0-0003	RPC	TB	DEC 12/00
2	UPDATED NOTES 1 & 5, ADDED 30M OPTION PER ECN # 99-865-0-0006	BG	SM	AUG 25/99
1	UPDATED NOTES & ADDED CABLE BOX	BG	SM	APR 22/99
0	FOR ISSUE	BG	SM	AUG 05/98
Rev	ECN/Description	Drw	Appr	Date

DIMENSIONS ARE IN INCHES				
USE DIMENSIONS ONLY- DO NOT SCALE				
THIRD ANGLE PROJECTION		PRODUCT GROUP:	ULTRASONICS	TOLERANCES UOS
		DATE:	05/AUG/98	1 PLC DECIMAL ±0.03
		DRAWN:	B. GRAY	2 PLC DECIMAL ±0.01
		CHECKED:	R. HARE	3 PLC DECIMAL ±0.002
		APPROVED:	S. MILLIGAN	ANGLES ±0.5°
		LOCATION:	PETERBOROUGH	SCALE
		SIEMENS MILLTRONICS PROCESS INSTRUMENTS INC PETERBOROUGH, ONTARIO CANADA		SIZE
		DRAWING No		B
		23650067		
		FILE No	23650067	
		PLOT AT 1:1	SHEET 1 OF 1	