

# The flexible power supply for a wide variety of applications



## All advantages at a glance

Maximum flexibility is required when supplying power to a variety of applications:

it can be 5 V one time, then 15 V and then possibly 46.5 V DC. For these applications, SITOP flexi is the smart solution.

With this universal power supply unit, you can easily set output voltages between 3 V and 52 V DC. All you need is this standard product – no need to waste time and money purchasing a whole range of different units. Save shipping and servicing costs too! Many additional features make applications possible that other conventional supplies just cannot match. Quite flexible, isn't it?

- Output continuously adjustable from 3 V to 52 V DC
- Dynamic adjustment of the output voltage also possible via analog input signal
- Many possible applications, e.g. motor speed control or test rig supply
- One universal supply can simplify configuring, servicing and spares backup, available from stock
- Remote diagnostics through floating relay contact as "Power Good" signal
- Load monitoring via integrated current monitor: output current value as analog signal
- Precise voltage at load thanks to remote sensing
- Constant current characteristic in case of overload ensures the start-up
- Standard DIN Rail mounting

# SITOP flexi


Answers for Industry.

**SIEMENS**

## Technical specifications

SITOP flexi		
<b>Input data</b>	Input voltage – Rated input voltage – Range	Single-phase AC voltage 120/230 V AC, adjustable using wire jumper 85 to 132/170 to 264 V AC
	Hold-up time	> 10 ms 93/187V and 120 W
	Mains frequency – Rated frequency – Range	50/60 Hz 47 to 63 Hz
	Input current – Rated value – Inrush current (+25 °C) – I <sup>2</sup> t – Integral input fuse – Recommended primary side protection	2.2/0.9 A < 32 A 0.8 A <sup>2</sup> s T 3.15 A (not accessible) 6 A characteristic C
<b>Output data</b>	Output voltage – Range of adjustment	Stabilized, floating DC voltage 3 ... 52 V DC, adjustable using potentiometer or remote-controlled via analog control voltage signal 0...2.5 V DC
	– Steady-state voltage tolerance – Residual ripple – Switching transients Output current, output power	1% < 50 mVpp < 100 mVpp Current limiting in range 3 to 12 V DC and power limiting in range 12 to 52 V DC
	– Max. output current (in range 3 to 12 V DC) – Max. output power (in range 12 to 52 V DC) – Current limiting	10 A 120 W 2 ... 10 A, adjustable using potentiometer or remote-controlled via analog control voltage signal 0 ... 2.5 V DC
	Efficiency at U <sub>I rated</sub> and 24 V DC/5 A output Parallel connection possible Electronic short-circuit protection Additional functions	Approx. 84% Yes Yes, constant current Sense line connection, power good signal (relay contact), current monitor
<b>RFI Specification</b>	RI suppression (EN 55022)	Class B
<b>Standards</b>	Protection class Electrical isolation (SELV to EN 60950) Degree of protection (EN 60529) Certification	Class I Yes IP20 CE, cULus-Listed (UL 508, CSA C22.2 No.142) File E143289
<b>General data</b>	Ambient temperature Storage and transport temperature Connections (solid or finely stranded conductors) – Connections for inputs L1, N, PE – Connections for output L + – Connections for output M Dimensions W x H x D in mm (in) Approx. weight kg (lbs)	0 to +60 °C –25 to +85 °C  1 x 0.5 to 2.5 mm <sup>2</sup> (20 AWG – 12 AWG) each 1 x 0.5 to 2.5 mm <sup>2</sup> (20 AWG – 12 AWG) 2 x 0.5 to 2.5 mm <sup>2</sup> (20 AWG – 12 AWG) 75 x 125 x 125 (2.95 x 4.92 x 4.92) 0.9 (2)
<b>Ordering data</b>	Order No.	6EP1353-2BA00

### Output characteristic



1) Range of adjustment for output voltage

2) Range of adjustment for current limiting

Siemens AG  
Industry Sector  
Industry Automation  
P.O. Box 32 55  
90713 FÜRTH  
GERMANY

[www.siemens.com/sitop](http://www.siemens.com/sitop)

Subject to change without prior notice  
Order No. E80001-A2120-P310-V2-7600  
DISPO 06305  
MK.SE.ST.SITP.52.8.06 SB 03082.  
Printed in Germany  
© Siemens AG 2008

The information provided in this brochure contains merely general descriptions or characteristics of performance which in actual case of use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.