

Meet the world's most rugged flow measurement team.

The broadest scope of ultrasonic flow meters for toughest applications with SITRANS F US.



SITRANS F

The SITRANS F US family of in-line and clamp-on ultrasonic flowmeters goes beyond meeting your challenges. With this broad scope we offer you the best choice for crude oil, refined petroleum, and liquefied gas. Performance, accuracy, and ease of use give you the extra edge you need in the oil and gas business. When it comes to ultrasonic flowmeters, part of our Sensor Systems portfolio, Siemens delivers everything you want. And a little bit more.

More information: www.siemens.com/flow
Setting standards with Totally Integrated Automation.

Answers for industry.

