



SCE Guide Learning/ Training Document

Siemens Automation Cooperates with Education (SCE) | 08/2023

Offer SCE Learning/Training Documents

More than **100 didactic SCE Learning/Training Documents**

- **Designed for use in classes and lectures; individual adaptation possible**
- **Suitable for self-study**
- **For implementation of the SCE Digitalization Concept**
- **Available free-of-charge online in up to 8 languages**



Didactically adapted documents impart practice-based, effective and structured learning content


[↗ Learning/Training Documents](#)

Getting Started using SCE Learning/Training Documents


SCE Module and Concept Description (1) Overview

The module description offers you a **complete overview of the modules**, **explains the structure of the SCE learning/training documents** and **supports you in selecting relevant, interesting and technically suitable contents**.

TIA Portal modules / from V13





[➤ To document](#)



Obtain a quick overview of module offers and structure.

SCE Module and Concept Description (2)

Module overview & detailed overview of basic/advanced modules



Basic and advanced modules are presented in detail.

Guide to learning/training documents according to product technologies



TIA Portal modules



- IOT2000EDU
- S7-1500/1200/300
- ET 200SP
- WinCC Advanced with TP700 Comfort
- WinCC Basic with KTP700 Basic
- SCALANCE XC208/S615
- G120
- RF210R IO-Link
- PID controller
- SCL
- Graph
- SIMIT
- STEP 7
- TIA Portal from V13
- TIA Portal with PLCSIM Advanced, NX MCD



PPCS 7 modules



PCS 7

- V9.0
- V8.1
- V8.0
- V7.0



LOGO! / CNC modules



LOGO!

- LOGO! logic modules
0BA0 - 0BA8
- LOGO!Soft Comfort V8.0

CNC

- SinuTrain Operate V4.5
- SinuTrain V6.3




Classic modules



Previous products up to 2010

[↗ See Guide](#)

Didactical structure of the SCE learning/training documents



For details, see the SCE Module & Concept Description Page 12

[➤ To document](#)

Didactical structure to consolidate learning success and provide helpful feedback.

What's new

SIEMENS Contact Global

Products & Services Market-specific Solutions Company Search

Home > Company > Sustainability > Education & Learning > SCE > Learning & Training Documents

Learning & Training Documents

Time-tested, curriculum-based and adaptable learning materials

Specifically designed for educational institutions (research, development and non-commercial institutions that provide initial training) in the fields of automation and drive technology, we offer more than 100 didactically prepared learning and training documents – including projects – for download free of charge. Our learn- & training documents are perfectly matched to curricula and syllabuses and are optimally suited for use with our SCE trainer packages. They also take into account all aspects of a modern industrial solution: installation, configuration, programming, and commissioning. They are based on Massive Open Online Course (MOOC) and blended learning concepts for conveying know-how on Industry 4.0. Pedagogics 3.0 concepts and learning as a service contribute to the high quality of our learn-/training documents. All documents can be individually matched to your requirements. Take advantage of our industrial know-how for the practice-oriented, efficient design of your courses.

Download

The SCE learning & training documents are subdivided into autonomous modules for the various topics, which can be customized according to the reader's knowledge.

Guided Tour

Here for the first time – just start with our guide. You will get a quick overview and recommendations for prepared SCE courses based on our modules.

[> What's new?](#) [> Guide](#)

What's new?

The latest learning & training documents

2021-05	070-XXX Safety	ES IT
2021-02	070-XXX Safety	DE EN
	150-XXX Digital Twin: Modules 1 to 6	PT
2021-01	062-121 Servo Drive S210 PN on PROFINET IRT with Technology Objects in SIMATIC S7-1500	FR PT
2020-11	000-000 Module and Concept Description	DE EN ES FR IT KR PT ZH
2020-10	062-121 Servo Drive S210 PN on PROFINET IRT with Technology Objects in SIMATIC S7-1500	ES IT ZH
2020-09	062-121 Servo Drive S210 PN on PROFINET IRT with Technology Objects in SIMATIC S7-1500	DE EN
2020-08	150-XXX Digital Twin: Modules 1 to 6	ZH
2020-07	150-XXX Digital Twin: Modules 1 to 6	FR
2020-06	150-XXX Digital Twin: Modules 1 to 6	IT
2020-04	150-XXX Digital Twin: Modules 1 to 6	EN ES
2020-03	150-XXX Digital Twin: Modules 1 to 6	DE
2020-01	500-XXX Process Automation (PA) – University Learn-/Training Documents V9.0	DE EN
2019-10	052-100 Sequencer Programming with GRAPH and SIMATIC S7	DE EN ES FR IT PT ZH
2019-09	020-120 SIMIT Process Simulation – Basics of simulation creation	DE EN

You can always find the latest learning/training documents under What's new.

Overview TIA Portal modules

050 Advanced Programming

The learning/training documents on TIA Portal have a modular structure and cover the following topics:

- Hardware Configuration
- Example Processes
- Basics of PLC Programming
- Visualization
- Advanced Programming
- Drives

They are designed for the SIMATIC controllers IOT2000EDU, S7-1500, S7-1200 and S7-300.

Getting Started, Videos, Tutorials, Apps, Manuals, Trial-SW/Firmware ← **Additional Links**

S7-1500 S7-1200

OXX-600 Summary Learn-/Training Document S7-1500 +

052-100 Sequencer Programming with GRAPH and SIMATIC S7 x

In this chapter, you will learn how to program a sequence control with the graphic programming tool S7-GRAPH and about the basic elements of a control program written with GRAFCET.

Learn-/Training document (DOC)	DE	EN	ES	FR	IT	PT	ZH
Learn-/Training document (PDF)	DE	EN	ES	FR	IT	PT	ZH
Projects (ZIP)	DE	EN					
Documentation (PDF)	DE	EN					

*Free download
of desired document
in up to 8 languages including
projects & documentation*

Download area always has an identical structure and downloads are always for free.

What's new: Course "DigitalTwin@Education"

150 Digital Twin

The Learning & Training Documents "DigitalTwin@Education" have a modular structure, include step-by-step instructions to make them easy to follow and cover the following topics:

- Module 1: Virtual commissioning of a provided virtual 3D sorting plant model with the TIA Portal, PLCSIM Advanced and NX MCD (Mechatronics Concept Designer)
- Module 2: Explanation of the specified automation program in TIA Portal for the control of the existing 3D sorting plant model
- Module 3: Presentation of possible modifications and optimizations of the automation program in TIA Portal for the provided virtual 3D sorting plant model
- Module 4: Modeling and creation of your own static 3D model for the sorting plan using the NX CAD system
- Module 5: Dynamization of the created 3D sorting plant model using the NX MCD CAE system
- Module 6 – in Preparation: Creation and mapping of the relevant signals for the automation program for the created 3D sorting plant model in NX MCD. In addition, validation of the desired functionality of the digital twin in interaction with the virtual controller in PLCSIM Advanced.

They are prepared for use with SIMATIC STEP 7 Professional V15 or higher, SIMATIC WinCC Advanced V15 or higher, PLCSIM Advanced V2.0 or higher and NX MCD V12.0 or higher.

150-001 Virtual commissioning of a production plant using a dynamic 3D model ✕

The following pages show how you can perform virtual commissioning of the dynamic 3D model using the TIA Portal and a WinCC HMI. The CAD tool NX V12.0 and the CAE add-on Mechatronics Concept Designer V12.0 were used to create the dynamic 3D model.

Learn-/Training document (DOC)	DE	EN	ES	FR	IT			ZH
Learn-/Training document (PDF)	DE	EN	ES	FR	IT			ZH
Projects (ZIP)		EN						

150-002 Configuration of the Automation Program of a Dynamic 3D Model in the TIA Portal +

150-003 Enhancements and Optimizations of an Automation Program for a 3D Model +

150-004 Creating a Static 3D Model Using the NX CAD System +


150-005 Creation of a Dynamic 3D Model Using the Mechatronics Concept Designer CAE System +

150-006 Signal Creation for a Dynamic 3D Model in the Mechatronics Concept Designer CAE System +

Teach the Digital Twin in your class in a simple manner with step-by-step instructions.

Recommendation: Prepared courses

Recommendation: Implement prepared courses with SCE learning/training documents



Perform "Knowledge transfer" for your students/trainees or for your own further training through step-by-step instructions with SCE learning/training documents.

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
LOGO! course	Basic Course on programming of LOGO!	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic knowledge of automation technology 	<ul style="list-style-type: none"> LOGO! logic module: 900-010 	<ul style="list-style-type: none"> Information about the use of LOGO! logic modules Getting started with LOGO! Terminal blocks and block numbers of LOGO! Logic operations Block representation in the display of LOGO! The four golden rules for operating LOGO! Overview of the LOGO! menus Example task factory gate control system Program input in LOGO! Parameter assignment to a block Starting and testing the program Debugging in LOGO! Programming and debugging with LOGO! Soft Comfort 	2
TIA Portal course	Basic Course for PLC programming with SIMATIC S7 and TIA Portal  <i>Our recommendation: Start with this basic course</i>	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic knowledge of automation technology 	<ul style="list-style-type: none"> Hardware configuration S7-1200 modules: 011-100 011-101 011-102 Hardware configuration S7-1500 modules: 012-100 012-101 012-105 Hardware configuration S7-300 module: 013-101 Process description module: 020-100 Programming S7-1200 modules: 031-100 031-200 031-300 031-410 Programming S7-1500 modules: 032-100 032-200 032-300 032-410 	<ul style="list-style-type: none"> Field of application and configuration of SIMATIC S7 device types Operation and function of SIMATIC S7 Creating a project with TIA Portal Configuring an SIMATIC S7 station in TIA Portal Writing, testing and storing program blocks in TIA Portal Addressing and program representation (LAD, FBD) Program structure and program blocks (OB, FB, FC and DB) Basic operation set Symbolic addressing Online test and diagnostic functions Tag declaration in function blocks (FB) and functions (FC) Creating a program example with tag declaration and data block Standard and system functions (IEC timer/ IEC counter) News for programming SIMATIC S7 with TIA Portal 	2

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
TIA Portal course	Advance Training Course for PLC programming with SIMATIC S7 and TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic course SIMATIC S7 with TIA Portal 	<ul style="list-style-type: none"> Hardware configuration S7-1200 module: 011-100 Hardware configuration S7-1500 module: 012-100 Hardware configuration S7-300 module: 013-101 Process description module: 020-100 Programming S7-1200 modules: 031-420 031-500 031-600 Programming S7-1500 modules: 032-420 032-500 032-600 	<ul style="list-style-type: none"> Brief review of the basic course with TIA Portal Data types and data blocks in SIMATIC S7 Program example with data block in TIA Portal Application examples for structured programming with FCs, FBs and DBs Extended instruction set and mathematical functions Reading, outputting and scaling analog values Application example for analog value processing in TIA Portal Test and diagnostic functions in TIA Portal <ul style="list-style-type: none"> Monitoring hardware online Module and operating status Monitoring, controlling and forcing inputs and outputs Exercises for troubleshooting and diagnostics with TIA Portal Error localization and error elimination at SIMATIC S7 <ul style="list-style-type: none"> Hardware diagnostics and diagnostic buffer Additional functions in the target system of the controller Comparing reference data, block assignment and program structure as well as blocks Error organization blocks at SIMATIC S7 Diagnostics and error messages for SIMATIC S7 via the integrated Web server 	2
TIA Portal course	Conversion Course from STEP 7 Classic to the TIA Portal with SIMATIC S7	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic knowledge of automation technology Basic knowledge of PLC programming with STEP 7 Classic <p><i>Note: This course is intended for users converting from STEP 7 Classic</i></p>	<ul style="list-style-type: none"> Hardware configuration S7-1200 modules: 011-100 011-101 011-102 Hardware configuration S7-1500 modules: 012-100 012-101 012-105 012-110 Hardware configuration S7-300 module: 013-101 Process description modules: 020-100 Programming S7-1200 modules: 031-100 031-200 031-300 031-410 Programming S7-1500 modules: 032-100 032-200 032-300 032-410 	<ul style="list-style-type: none"> Field of application and configuration of the new SIMATIC S7 controllers Creating a project with TIA Portal Configuring an SIMATIC S7 station in TIA Portal Writing, testing and storing program blocks in TIA Portal Addressing and program visualization with LAD and FBD Program structure and program blocks with OB, FB, FC and DB Symbolic addressing Online/test and diagnostics functions Tag declaration in function blocks (FB) and functions (FC) Creating a program example with tag declaration and data block Standard and system functions (IEC timer/ IEC counter) News for programming a SIMATIC S7 with TIA Portal 	2

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
TIA Portal course	Process Visualization with SIMATIC WinCC Basic and SIMATIC S7-1200 in the TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC Advance Course SIMATIC S7 with TIA Portal 	<ul style="list-style-type: none"> WinCC Basic with KTP700 Basic and SIMATIC S7-1200 module: 041-101 	<ul style="list-style-type: none"> Visualization systems in automation engineering Process control system with SIMATIC WinCC Basic and TIA Portal System description Project structure Creating a process control system with SIMATIC WinCC Basic Starting WinCC Basic and creating projects Specifying the tag management Creating process pictures Controlling process values and representing process values Setting the Runtime properties of the computer/panel and starting Runtime Integrating graphics with SIMATIC WinCC Basic Archiving and displaying measured values with WinCC Basic Alarm logging of SIMATIC WinCC Basic 	2
TIA Portal course	Process Visualization with SIMATIC WinCC Advanced and SIMATIC S7-1500 in the TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC Advance Course SIMATIC S7 with TIA Portal 	<ul style="list-style-type: none"> WinCC Advanced with TP700 Comfort and SIMATIC S7 module: 042-201 	<ul style="list-style-type: none"> Visualization systems in automation engineering Process control system with SIMATIC WinCC Advanced and TIA Portal System description Project structure Creating a process control system with SIMATIC WinCC Advanced Starting WinCC Advanced and creating projects Specifying the tag management Creating process pictures Controlling process values and representing process values Setting the Runtime properties of the computer/panel and starting Runtime Integrating graphics with SIMATIC WinCC Advanced Archiving and displaying measured values with WinCC Advanced Alarm logging system of SIMATIC WinCC Advanced 	2

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
TIA Portal course	Basics of PROFIBUS and PROFINET with the TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic course SIMATIC S7 with TIA Portal 	<ul style="list-style-type: none"> Hardware configuration SIMATIC S7-1500 and ET200SP via PROFINET module: 012-201 	<ul style="list-style-type: none"> Fieldbus systems in automation engineering Requirements for a bus system Hierarchy levels in automation engineering General information about fieldbus systems Technical specifications and functionality of PROFINET/PROFIBUS Bus configuration and network structure Components for configuring PROFINET/PROFIBUS PROFINET/PROFIBUS network components Remote programming via PROFINET/PROFIBUS I/O controllers and field devices on PROFINET/PROFIBUS Commissioning PROFINET with a SIMATIC S7 I/O controller and ET 200 I/O devices Commissioning PROFIBUS with a SIMATIC S7 master and ET 200 slaves Optional: CPU/CPU communication on PROFINET/PROFIBUS 	2
TIA Portal course	Safety Integrated Safety Engineering on PROFINET with SIMATIC S7 in the TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC SIMATIC S7 continuation course with the TIA Portal, bus systems with SIMATIC S7 	<ul style="list-style-type: none"> PROFIsafe and PROFINET with ET 200SP and SIMATIC S7-1500 module: 072-100 	<ul style="list-style-type: none"> Basic information for the integration of machine safety Regulations and standards Risk analysis General information on fieldbus systems in use for personal safety Components for configuring a safety-related application on PROFINET Safety Integrated with SIMATIC S7 in the TIA Portal Fail-safe communication with PROFIsafe I/O components for PROFIsafe Safety-related programming with the STEP 7 Safety software in the TIA Portal Commissioning and programming of PROFIsafe with SIMATIC 1500 and ET 200SP Error diagnostics and error analysis for safety engineering application in the TIA Portal Optional: Fail-safe CPU/CPU communication in the TIA Portal with SIMATIC S7 	2

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
TIA Portal course	Application for Industrie 4.0 Industrial Networking IT Security / OPC UA with the TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic course SIMATIC S7 with TIA Portal 	<ul style="list-style-type: none"> Advanced Communication modules - OPC UA with SIMATIC S7-1500 and Node-RED: 092-300 092-303 Security module - Industrial Ethernet with SIMATIC S7-1500 and SCALANCE XC208: 142-100 Security module - Industrial Security with SIMATIC S7-1500 and SCALANCE S615: 142-200 	<ul style="list-style-type: none"> Industrie 4.0 - Driving the Digital Enterprise IT security with OPC / Ethernet / PROFINET General information on OPC UA / Ethernet / PROFINET Applications for IT security on Industrial Ethernet Applications for IT security on PROFINET Technical specifications and functionality of OPC UA OPC UA – Open communication in the TIA Portal with SIMATIC S7-1500 Commissioning OPC UA with SIMATIC S7-1500 as a server and Node-RED as client Other OPC UA clients such as TP700, Excel, etc. 	2
TIA Portal course	Application for Industrie 4.0 Industrial Networking PROFINET / IO-Link / RFID with the TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic course SIMATIC S7 with TIA Portal 	<ul style="list-style-type: none"> Hardware configuration S7-1500 module: 012-100 RFID Sensor Technology with RF210R IO-Link, ET 200SP and SIMATIC S7-1500 module: 102-101 	<ul style="list-style-type: none"> Industrie 4.0 - Driving the Digital Enterprise Networking with Industrial Ethernet and PROFINET Bus configuration and network structure of PROFINET Commissioning of PROFINET (I/O controller and I/O device) with the TIA Portal Topology, network diagnostics in the TIA Portal Intelligent connection of sensors and switchgear with IO-Link Commissioning of IO-Link on PROFINET with ET 200SP RFID sensor technology Commissioning of RFID sensor RF 210R on IO-Link Integrated diagnostics for PROFINET / IO-Link / RFID 	2

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
TIA Portal course	Basic Course: SCL High-Level Language with SIMATIC S7 and TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC Advance Course SIMATIC S7 with TIA Portal 	<ul style="list-style-type: none"> SCL and SIMATIC S7-1200 module: 051-201 SCL and SIMATIC S7-1500 module: 052-201 	<ul style="list-style-type: none"> Brief review of the SIMATIC S7 control system Creating a project with the TIA Portal Configuring an S7 station Working with the SCL editor Customizing the SCL user interface Creating user programs in SCL Entering declarations, instructions and comments Description of SCL language The compiling process Selection and assignment of the possible block types Specification of the block interfaces in SCL Continuous monitoring Activating breakpoints Monitoring/forcing tags Reference data 	2
TIA Portal course	Machining Step Programming with GRAPH in the TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic course SIMATIC S7 with TIA Portal 	<ul style="list-style-type: none"> GRAPH and SIMATIC S7 module: 052-100 	<ul style="list-style-type: none"> Possible representations of sequencers; GRAFCET GRAPH programming software as a component of TIA Portal Creating a project with hardware configuration and symbol table in STEP 7 Elements of a sequencer in GRAPH (step / transition / branch / jump / etc.) Creating and compiling a sequencer with GRAPH Downloading a machining step program to PLC and testing it Monitoring the sequencer in GRAPH and other diagnostic functions Sequence control with GRAPH Synchronizing the sequencer with the process Machining step programming with constraints Input/output parameters of the GRAPH function blocks Interlock functions in GRAPH (Interlock) Supervision functions in GRAPH (Supervision) 	2

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
TIA Portal course	Basics for Programming an IOT2000	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic knowledge of automation engineering and the C programming language 	<ul style="list-style-type: none"> Hardware configuration IOT2000 module: 014-101 FC-Programming IOT2000 module: 034-100 OPC-UA and Node-RED with SIMATIC IOT2000 modules: 092-300 / 092-303 / 094-100 	<ul style="list-style-type: none"> Information on areas of application and structure of IOT2000 Introduction to SIMATIC IOT2000 Applications with the IOT2000 (Node-RED, Arduino, OPC client, S7 connection with Node-RED, etc.) Commissioning of IOT2000 including TIA Runtime Addressing the IOT2000 GPIOs Creating a project with the TIA Portal Configuring a SIMATIC S7 station in the TIA Portal Writing, testing and storing program blocks in the TIA Portal 	2
TIA Portal course	Frequency Converter SINAMICS G120 on PROFINET with SIMATIC S7 and TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC Advance Course SIMATIC S7 with TIA Portal 	<ul style="list-style-type: none"> Frequency Converter G120 on PROFINET with SIMATIC S7-1500 module: 062-101 	<ul style="list-style-type: none"> Presentation of the SINAMICS frequency converters from SIEMENS Drive configuration with the SIZER software Commissioning and parameter assignment of these converters with SINAMICS Startdrive Structure of the parameter assignment with authorization levels Parameter assignment of SINAMICS G120 Commissioning with asynchronous motor Troubleshooting Connection of a frequency converter to a SIMATIC S7 PLC via PROFINET Communication structure of PROFINET Commissioning a SIMATIC S7 PLC as an IO controller Setting up the frequency converter as an IO device on PROFINET Remote control of the frequency converter via PROFINET Remote parameter assignment of the frequency converter via PROFINET Remote diagnostics for the frequency converter via PROFINET Parameter assignment with the SINAMICS Startdrive software in the TIA Portal Optional: Motion Control technology objects for S7-1500 	2

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
TIA Portal course	Control technology SIMATIC S7 with TIA Portal	<ul style="list-style-type: none"> Basic knowledge of Windows PC Advance Course SIMATIC S7 with TIA Portal 	<ul style="list-style-type: none"> Programming S7-1200 module: 031-500 Programming S7-1500 module: 032-500 Extended programming S7-1200 module: 051-300 Extended programming S7-1500 module: 052-300 	<ul style="list-style-type: none"> Controllers in automated plants Software controller for SIMATIC S7 in TIA Portal Design steps and modeling in controlling of process variables Quality requirements for the control loop Controller structures Controller parameters and adjustment procedure Controller testing Data types at SIMATIC S7 Mathematical functions and data type conversion Reading, outputting and scaling analog values Developing a program for two-step controllers in TIA Portal Testing the program for two-step controllers and commissioning with processes Controller block as software PID controller Configuring an SIMATIC S7 station in TIA Portal Integrating and configuring the PID controller software in STEP 7 programs with TIA Portal Setting and configuring the PID controller software in TIA Portal Commissioning the PID controller software with processes 	2
TIA Portal course	Project Work and Commissioning of Industrie 4.0 System with Application Examples for Different IEC 61131 Programming Languages	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic knowledge of control engineering/STEP 7 		<ul style="list-style-type: none"> To be individually coordinated with the system of the customer or the systems used elsewhere 	2

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
TIA Portal course	SIMIT SCE – Simulating Plants Dynamically on the PC	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic course SIMATIC S7 	<ul style="list-style-type: none"> Process description sorting station module: 020-100 SIMIT process simulation – coupling modules: 020-110 / 020-111 / 020-112 SIMIT process simulation – basics module: 020-120 	<ul style="list-style-type: none"> General information about SIMIT Installing the SIMIT software Managing and setting up projects General procedure for creating a project Setting up a new project Configuration of the interface to PLCSim / PLCSim Advanced / OPC UA Configuring an operating screen General information about animation of screens Component types and components Assigning component parameters Creating example projects Starting the simulator and testing the programs Connection to real PLC 	2
TIA Portal course	DigitalTwin@Education	<ul style="list-style-type: none"> Basic and advanced knowledge of TIA Portal/PLCSIM Advanced und NX MCD 	<ul style="list-style-type: none"> Modul 1: 150-001 Virtual commissioning of a production plant using a dynamic 3D model Modul 2: 150-002 Configuration of the Automation Program of a Dynamic 3D Model in the TIA Portal Modul 3: 150-003 Enhancements and Optimizations of an Automation Program for a 3D Model Modul 4: 150-004 Creating a Static 3D Model Using the NX CAD System Modul 5: 150-005 Creation of a Dynamic 3D Model Using the Mechatronics Concept Designer CAE System Modul 6: 150-006 Signal Creation for a Dynamic 3D Model in the Mechatronics Concept Designer CAE System 	<ul style="list-style-type: none"> Module 1: Virtual commissioning of a provided virtual 3D sorting plant model with the TIA Portal, PLCSIM Advanced and NX MCD (Mechatronics Concept Designer) Module 2: Explanation of the specified automation program in TIA Portal for the control of the existing 3D sorting plant model Module 3: Presentation of possible modifications and optimizations of the automation program in TIA Portal for the provided virtual 3D sorting plant model Module 4: Modeling and creation of your own static 3D model for the sorting plan using the NX CAD system Module 5: Dynamization of the created 3D sorting plant model using the NX MCD CAE system Module 6 – in Preparation: Creation and mapping of the relevant signals for the automation program for the created 3D sorting plant model in NX MCD. In addition, validation of the desired functionality of the digital twin in interaction with the virtual controller in PLCSIM Advanced. <p>They are prepared for use with SIMATIC STEP 7 Professional V15 or higher, SIMATIC WinCC Advanced V15 or higher, PLCSIM Advanced V2.0 or higher and NX MCD V12.0 or higher.</p>	5

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
TIA university courses	University Workshop: TIA Portal with SIMATIC S7-1500, ET 200SP on PROFINET and Visualization with WinCC Advanced	<ul style="list-style-type: none"> Basic knowledge of automation engineering with SIMATIC 	<ul style="list-style-type: none"> Hardware configuration S7-1500 module: 012-100 Hardware configuration S7-1500 module and ET 200SP: 012-201 Process description module: 020-100 Programming S7-1500 modules: 032-200 032-300 032-410 032-420 Visualization module: 042-201 Frequency Converter G120 on PROFINET with SIMATIC S7-1500 module: 062-101 	<ul style="list-style-type: none"> TIA Portal: New information about SIMATIC S7-1200/1500 PLCs Safety and security with SIMATIC S7-1200/1500 More efficient programming and configuration with the TIA Portal and SIMATIC S7-1500 New commands and functions of SIMATIC S7-1200/1500 Programming examples for SIMATIC S7-1500 Test and diagnostic functions for SIMATIC S7-1500 Remote programming and web services for SIMATIC S7-1500 Commissioning of PROFINET with the TIA Portal: SIMATIC S7-1500 as IO controller and ET 200SP as IO device Process visualization in the TIA Portal with WinCC Example application for WinCC with the TIA Portal and Comfort Panel TP700 Commissioning and parameter assignment of these converters with SINAMICS Startdrive Connection of a frequency converter to a SIMATIC S7 PLC via PROFINET 	2
PCS 7 University course	PA Basic Course for Process Automation with SIMATIC PCS 7 Process Control System	<ul style="list-style-type: none"> Basic knowledge of SIMATIC S7 Process visualization basic knowledge 	<ul style="list-style-type: none"> PA university curriculums for SIMATIC PCS 7 modules: P01-00 to P01-08 	<ul style="list-style-type: none"> Introduction to process control system SIMATIC Process Control System PCS 7 Process description and system structure SIMATIC Manager and hardware configuration Plant hierarchy in SIMATIC PCS 7 Continuous Function Chart (CFC) <ul style="list-style-type: none"> Individual control functions with CFC Plant safety with CFC Control technology with CFC Programming sequential control systems with Sequential Function Chart (SFC) SIMATIC PCS 7 graphic generation for the operator station 	2

Detailed overview: Prepared technologies for knowledge transfer

Course type	Course	Prerequisites	SCE Learn-/Training Documents	Contents	Days
PCS 7 University course	PA Advance Course for Process Automation with SIMATIC PCS 7 Process Control System	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic knowledge of process control technology with SIMATIC PCS 7 basic knowledge of Windows PC 	<ul style="list-style-type: none"> PA university curriculums for SIMATIC PCS 7 modules: P01-01 P02-01 to P02-03 P03-01 P03-02 	<ul style="list-style-type: none"> Commissioning PCS 7 project from basic course Repetition and details of programming with CFC and SFC in PCS 7 Alarm Engineering and alarm system in PCS 7 Bulk processing and reusability of structures in PCS 7 Archiving Trend reporting and trend display in PCS 7 Advanced operator control design with ActiveX controls and user-defined objects Vertical integration with OPC 	2
Sinu Train course	Basics of CNC technology with SinuTrain	<ul style="list-style-type: none"> Basic knowledge of Windows PC Basic knowledge of NC technology 	<ul style="list-style-type: none"> CNC technology modules: 700-010 700-020 700-030 	<ul style="list-style-type: none"> Basic concept and configuration versions of SinuTrain as training software for SINUMERIK controllers Handling of control components of SinuTrain Manual functions and screen layout Setup and measuring of tools Work offsets Practical commissioning of the machine tool Part program management and program editor Creating a simple workpiece according to DIN 66025 Programming DIN standard cycles with SinuTrain Simulation functions in SinuTrain Machining of the workpiece with the machine tool Special characteristics of SHOPMILL and SHOPTURN Work step programming Program creation with the contour calculator CAD reader Data backup and data transmission Programming milling parts with SHOPMILL Programming lathed parts with SHOPTURN 	2

SCE Guide Learning/Training Documents Feedback & additional links

Siemens Automation Cooperates with Education (SCE)

Teach and learn what matters! The digital transformation is in full swing. SCE provides educators with a comprehensive offering to convey industry 4.0/automation knowledge for academia and in-house vocational training, which can also be used by learners for self-study.

[SCE Support Finder](#)



SiePortal registration guide
for download of restricted export goods, services, software, application examples, learning/training documents and more

Registration made easy for SiePortal

For the download of restricted export goods, services, software, application examples, learning/training documents and more, registration is required for all companies, educational institutions, educators, trainers, students and trainees. A new SCE explanatory video makes the registration process easier for everyone.

If you have any questions about completing the registration form, please contact your local [SCE contact](#).

Watch video:

[DE](#) [EN](#) [ES](#) [FR](#) [IT](#) [ZH](#)

[Register now](#)

[SCE Support Finder](#)

 <p>Learning/Training Material</p> <ul style="list-style-type: none"> • Downloads • Guided tour • What's new? • Courses 	 <p>Trainer Packages & Products</p> <ul style="list-style-type: none"> • Trainer Packages • SIMATIC IOT2000 	 <p>Learning Systems</p> <ul style="list-style-type: none"> • Manufacturers of Learning Systems
 <p>Text books</p> <ul style="list-style-type: none"> • Downloads 	 <p>Media Support</p> <ul style="list-style-type: none"> • Media Support 	 <p>Technical Support</p> <ul style="list-style-type: none"> • Industry Online Support • Trial software / firmware • Getting Started / WBT • Use Cases • Products & Systems
 <p>WorldSkills</p> <ul style="list-style-type: none"> • Competitions • Cooperation 	 <p>Trainees & Students</p> <ul style="list-style-type: none"> • Overview • Jobs & Career • Application Tips 	 <p>Contact partner</p> <ul style="list-style-type: none"> • Overview

Comprehensive support for educators and students on the way to Industry 4.0



Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

All product designations may be trademarks or other rights of Siemens AG, its affiliated companies or other companies whose use by third parties for their own purposes could violate the rights of the respective owner.

[siemens.com/sce](https://www.siemens.com/sce)