

Flat Rate Repair Structure for Out of Warranty

Product Line	Product	Repair Price Canadian \$\$	Rush Charge	Total Incl Rush Canadian \$\$
ULTRASONICS	Continuous Level			
	7ML1810 - AO10	Contact Factory		
	7ML1025/1028 - HYDRO +	\$650.00	\$130.00	\$780.00
	7ML1022 - HYDRO SM	No repair		
	7ML1034 - HYDRORANGER	\$650.00	\$130.00	\$780.00
	7ML5034 - HYDRORANGER	\$650.00	\$130.00	\$780.00
	7ML1016-1 - MINIR + /RM/PM	No repair		
	7ML1020 - MULTI+SM	No repair		
	7ML1033 - MULTIRANGER	\$650.00	\$130.00	\$780.00
	7ML5033 - MULTIRANGER	\$650.00	\$130.00	\$780.00
	7ML1002 - OCM	Contact Factory		
	7ML1010 - CRANERANGER	Contact Factory		
	7ML1013 - DPS300	Contact Factory		
	7ML1001 - ENVIRORANGER	\$650.00	\$130.00	\$780.00
	PROGL	No repair		
	7ML1811 - SAM20	Contact Factory		
	TEMPSENS	No repair		
	7ML1004 - SPL /DPL	\$650.00	\$130.00	\$780.00
	7ML5004 - SITRANS LU 01 / LU 02	\$650.00	\$130.00	\$780.00
	7ML5007 - SITRANS LU 10	\$650.00	\$130.00	\$780.00
	7ML1007 - XPL +	\$650.00	\$130.00	\$780.00
	7ML60 - LT500	\$650.00	\$130.00	\$780.00
	7ML5050 - LUT400	\$650.00	\$130.00	\$780.00
	Transducers			
	LR SERIES	No repair		
	7ML1100 - STH	No repair		
	7ML1136 - XCT12	No repair		
	7ML1132 - XCT8	No repair		
	7ML1105/1106/1109 - XRS5	No repair		
	7ML1170 - XPS10F	No repair		
	7ML1115 - XPS10	No repair		
	7ML1118/1161/1171 - XPS15	No repair		
	7ML1123/1155 - XPS30	No repair		
	7ML1127 - XPS40	No repair		
	7ML1158 - XPS40C	No repair		
	Probe			
	7ML5221 - PROBE LU	No repair		
	7ML51 - LU240	No repair		
	7ML5201 - LU150	No repair		
	7ML5202 - LU180	No repair		
	7ML5430 - PROBE LR	No repair		
	7ML1201 - PROBE2W	No repair		
	7ML1201 - PROBE3W	No repair		
	7ML1201 - PROBEIS	No repair		
	7ML1201 - PROBEEXT	No repair		
	7ML1201 - HPROBE	No repair		
	Point level			
	STOCKTROL	Contact Factory		
	7ML1510 - POINTEK ULS	No repair		
	MASS DYNAMICS	Continuous Weighing		
7MH7164/7MH7175 - PLS/VLS		Contact Factory		
COMPUSCALE		No repair		
7MH7122 - MSI (Global)		Contact Factory		
7MH7125 - MCS (Global)		Contact Factory		
7MH7120/7123 - MUS (Global)		Contact Factory		
7MH7177 - WS300 Speed Sensor		Contact Factory		
7MH7130 - MD256 repl by WS300		Contact Factory		
7MH7132 - MD256 repl by WM100		Contact Factory		
7MH7158 - WM100		Contact Factory		
7MH7134 - RB55		Contact Factory		
SF500 - 7MH7156		\$650.00	\$130.00	\$780.00
7MH7150 - BW100		No repair		
7MH7152 - BW500		\$650.00	\$130.00	\$780.00
7MH7110 - ILE37 (Global)		Contact Factory		
7MH7112 - ILE61 (Global)		Contact Factory		
7MH7100 - MILLFLO (Global)		Contact Factory		
LOADCELL		No repair		
WF400 (Global)		Contact Factory		
WF600 (Global)		Contact Factory		
WF800 (Global)		Contact Factory		
WF1200 (Global)		Contact Factory		
WFCUST (Global)		Contact Factory		
WFSP (Global)		Contact Factory		
7MH7180 - WW100		Contact Factory		
WW200		Contact Factory		
WW300		Contact Factory		
Process Protection				
7MH7144 - MFA4P		\$250.00	\$50.00	\$300.00
7MH7142 - MILLPULSE		No repair		
MSP12 - 7MH7146		No repair		
PREAMP		No repair		
XPP5		No repair		
ZEROSS		No repair		
7MH7562 - SENACOCU		\$250.00	\$50.00	\$300.00
7MH7560 - AS100		No repair		

Flat Rate Repair Structure for Out of Warranty				
MICROWAVE	Radar			
	7ML530 - LR100	Contact Factory		
	7ML531- LR110	Contact Factory		
	7ML532 - LR120	Contact Factory		
	7ML533 - LR140	Contact Factory		
	7ML534 - LR150	Contact Factory		
	7ML5422 - LR200	No repair		
	7ML5423/5424/5425 - LR200	\$900.00	\$180.00	\$1,080.00
	7ML5431 - LR250	\$900.00	\$180.00	\$1,080.00
	7ML5432 - LR250 Flange Encap Ant.	\$900.00	\$180.00	\$1,080.00
	7ML5433 - LR250 ENCAPHGA	\$900.00	\$180.00	\$1,080.00
	7ML5427 - LR260	\$900.00	\$180.00	\$1,080.00
	7ML5413/5412/5411 - LR 300	No repair		
	7ML5420/5421 - LR400	No repair		
	LR400 Retro fit to LR460	\$900.00	\$180.00	\$1,080.00
	7ML5426 - LR460	\$900.00	\$180.00	\$1,080.00
	7ML5440 - LR560	\$900.00	\$180.00	\$1,080.00
CAPACITANCE	Capacitance			
	7ML5501/5610 - CLS100	No repair		
	7ML5502/5504/5505 - CLS200	No repair		
	7ML5630/5631/5632/5633/5634/5640/5641/5642/5643/5644 CLS200	No repair		
	7ML5503/5506/5507/5508 - CLS300	No repair		
	7ML5650/5651/5652/5660/5661/5662 - CLS300	No repair		
	7ML5601/5602/5603/5604 - CLS500	Contact Factory		
	7ML5605/5606 - LC300 SITRANS	Contact Factory		
	7ML5670/5671/5672/5673 - LC300	Contact Factory		
	7ML5511, 5512, 5513, 5514, 5515, 5516, 5517, 5518- LC500 SITRANS	Contact Factory		
	Third party products	Hardware		
LEVELWATCH		No Repair		
7ML5710,5712,5714, 5725,5726, 5727,5728,5730 - LPS200		Contact Factory		
7ML5720,5722, 5724,5731,5732, 5733, 5734 - LVS 200		Contact Factory		
7ML5735 - LVS 100		Contact Factory		
7ML5745 - LVL100		Contact Factory		
7ML5746, 5747 - LVL 200		Contact Factory		
VLS200 - 7MH7175		Contact Factory		
7ML1300,1301,1302,1303,1304, 1305 - LG 200		Contact Factory		
PLS200 - 7MH7164/6/8		Contact Factory		
SMARTLINX		No Repair		
VS-100 - 7ML1030		Contact Factory		

Surcharges	
Rush Charge	20% of Repair Costs
Evaluation Fee	\$200.00 CAD
- Includes No Faults Found	\$200.00 EUR
	\$200.00 USD
ReStocking Charge	based on the Siemens credit table